



VZ133N

Door, Volta, flush/hollow wall, tran.,3rows

Technische Merkmale

Architecture

Intended door position	left
Fixing mode	Screwed

Configuration

Version as door for disconnecting switch interlocking	no
---	----

Cover, door

Material thickness cover	1 mm
Type of door closing	Latch
Door type for switch gear cabinet	Stop door
Door leave	single
Door quantity	1
Door included	yes
Transparent cover or door	yes

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Type of surface treatment	untreated

Dimensions

Depth of installed product	36 mm
Height of installed product	570,5 mm
Width of installed product	288 mm
Built-in height	570,5 mm
Built-in width	288 mm

Installation, mounting

Suitable for outdoor use	no
--------------------------	----

Equipment

Number of rows	3
----------------	---

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK05
Protection index IP	IP30
Halogen free	no
Ultraviolet resistant	no

Shape	
Slotted	no