



VZ016M

## Cable gland, vector, IP65, M16

### Technische Merkmale

#### Functions

Strain relief possibility	yes
Suitable for nominal thread metric/PG	0 / 16

#### Materials

Colour	light grey
Material	plastic
Material quality	thermoplastic
Type of surface treatment	untreated

#### Mecanic features

Thread type	Metric
-------------	--------

#### Dimensions

thread gradient	1,5
Screw head size in mm	22 mm

#### Connection

Clamping range	5-10 mm
----------------	---------

#### Equipment

Screened	no
----------	----

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

Protection index IP	IP65
Halogen free	yes
Compliant Ex-Zone dust	none
Safe use in explosive atmosphere	no
For Ex-zone gas	no

#### Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------