



Insulated busbar 1P fork 20mm² 57M

Technische Merkmale

Architecture

Number of poles	1 P
-----------------	-----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

Voltage

Max operating voltage	230 V
-----------------------	-------

Electric current

Rated current	100 A
---------------	-------

Materials

Colour	stone grey
--------	------------

Dimensions

Length	1000 mm
Pitch	17,8 mm
Fixation distance in module steps	1

Installation, mounting

Suitable to a device with an auxiliary	no
--	----

Connection

Connection cross-sect. rigid cable	20mm²
Suitable for product with neutral busbar	no
Connector type	busbar fork
Type of connection	with screw

Equipment

Number of appliances to build in	57
----------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Insulated	yes
-----------	-----

KD190B