



KDN263B

Insulated busbar 2P fork 10mm² 57M

Technische Merkmale

Architecture

Number of poles	2 P
-----------------	-----

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	63 A
---------------	------

Materials

Colour	stone grey
--------	------------

Dimensions

Length	1000 mm
Pitch	17,8 mm
Fixation distance in module steps	2

Installation, mounting

Suitable to a device with an auxiliary	no
--	----

Connection

Connection cross-sect. rigid cable	10mm ²
Suitable for product with neutral busbar	yes
Connector type	busbar fork
Type of connection	with screw / quick connect

Equipment

Number of appliances to build in	28
----------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Insulated	yes
-----------	-----