



## Insulated busbar 3x(P+N) fork 16mm² 57M

### Technische Merkmale

#### Architecture

Number of poles	4 P
-----------------	-----

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

#### Voltage

Max operating voltage	400 V
-----------------------	-------

#### Electric current

Rated current	80 A
---------------	------

#### Materials

Colour	stone grey
--------	------------

#### Dimensions

Length	1000 mm
Pitch	17,8 mm

#### Installation, mounting

Suitable to a device with an auxiliary	no
--	----

#### Connection

Connection cross-sect. rigid cable	16mm²
Suitable for product with neutral busbar	yes
Connector type	busbar fork
Type of connection	with screw / quick connect

#### Equipment

Number of appliances to build in	54
----------------------------------	----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Insulated	yes
-----------	-----

KDN451E