



TU404



## 4-channel remote control

### Architecture

Number of keys	4
Fixing mode	other

### Functions

- ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
- easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
- reset function (to factory setting)
- quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

### Controls and indicators

- with configuration button
- with side locking buttons

### Connectivity

Radio protocol	KNX Radio
AM / FM Modulation	FM
Receiver category	2

### Frequency

Transmission frequency	868 MHz
Radio transmission frequency	868,3 MHz

### Power

Radio transmission power	< 10 mW
- low intrinsic energy requirement	

### Endurance

Transmitter duty cycle	1 %
------------------------	-----

#### Reach distance

Max. transmission range	30m in house / 100m free field
-------------------------	--------------------------------

#### Battery

Battery service life [years]	~ 5
autonomy	5 years

- with 2 x lithium coin cell battery 3 V type: CR 2430

#### Dimensions

Depth of installed product	15,8 mm
Height of installed product	83 mm
Width of installed product	46,5 mm
Dimensions (LLxwwxhh)	83 x 46,5 x 15,8 mm

#### LED control

- with configuration LED  
- with transmission status and battery status LED, red/green/orange

#### Connection

- integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system

#### Equipment

Number of radio channels	4
--------------------------	---

#### Safety

Protection index IP	IP50
---------------------	------

- with keyring

#### Use conditions

Operating temperature	-10 45 °C
-----------------------	-----------