



slotted panel trunking BA7 40x25, blue

Technische Merkmale

Architecture

Flexible	no
----------	----

Configuration

Side wall configuration	Slotted
Self-extinguishing	yes

Electric current

Current leak stable	yes
---------------------	-----

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	blue
Material	PVC
Material group	plastic
Type of surface treatment	untreated

Dimensions

Trunking height	40 mm
Length	2000 mm
Trunking width	25 mm
Slot width	6 mm
Tongue width	6,5 mm

Installation, mounting

Base punching	EN 50085-2-3:1999
Fixing type	bottom punching

Cable

Number of wires 1,5 mm ² - 40% filling degree	22
Internal/useful cross section	605 mm ²
Number of wires 2,5 mm ² - 40% filling degree	15
Number of wires 1,0 mm ² - 40% filling degree	30

Scope of delivery

Covers supplied with the product	yes
----------------------------------	-----

Standards

Approvals	EN50085-2-3
European directive RoHs	voluntary compliance
UL 94 classification	V0

BA740025BL

Safety

Halogen free	no
Fireproof classification	M1

temperatur

Ambient temperature	-5...60 °C
---------------------	------------