



HNG 50037/0 Grey 7035 Trunking

Technische Merkmale

Architecture

Flexible	no
----------	----

Configuration

Side wall configuration	Slotted
Self-extinguishing	yes

Electric current

Current leak stable	yes
---------------------	-----

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	PPO
Material group	plastic
Type of surface treatment	untreated

Dimensions

Trunking height	50 mm
Length	2000 mm
Trunking width	37 mm
Slot width	5 mm
Tongue width	7,5 mm

Installation, mounting

Base punching	EN 50085-2-3:1999
Fixing type	bottom punching

Cable

Number of wires 1,5 mm ² - 40% filling degree	69
Internal/useful cross section	1472 mm ²
Number of wires 2,5 mm ² - 40% filling degree	49
Number of wires 1,0 mm ² - 40% filling degree	96

Scope of delivery

Covers supplied with the product	yes
----------------------------------	-----

Standards

European directive RoHs	voluntary compliance
UL 94 classification	V1

HNG5003707035B

Safety

Halogen free	yes
--------------	-----

temperatur

Ambient temperature	-25...90 °C
---------------------	-------------