



KR15P

DIN rail terminal 35-150mm²

Technische Merkmale

Architecture

Fixing mode	on mounting rail according to DIN EN 50022
-------------	--------------------------------------------

Main electrical features

Rated operational voltage U _e	1000 V
------------------------------------------	--------

Electric current

Rated current	309 A
---------------	-------

Materials

Colour	stone grey
Colour	dark grey
Material	Polyamid (PA)

Dimensions

Depth of installed product	100 mm
Height of installed product	118,5 mm
Width of installed product	31 mm

Connection

Connection cross section (solid-core)	35, 150 mm ²
Connection cross section (fine-strand)	50, 150 mm ²
Connection cross-sect. flexible conductor	35 / 150mm ²
Connection cross-sect. rigid cable	35 / 150mm ²
Conductor cross-section (flexible), with wire end sleeve	50...150 mm ²
Conductor cross-section (flexible), without wire end sleeve	50...150 mm ²
Type of connection	with screw

Equipment

Number of clamp positions	2
Number of levels	1

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-60...105 °C
-----------------------	--------------