



LFF601167030



## End cap for LFF60110 and LFF40110 gr

### Technische Merkmale

#### Architecture

|             |                        |
|-------------|------------------------|
| Fixing mode | Clamping and screwable |
|-------------|------------------------|

#### Functions

|  |     |
|--|-----|
| Overlapping  | yes |
| Suitable for functional integrity according to DIN 4102-12 | no  |

#### Configuration

|                         |    |
|-------------------------|----|
| Antibacterial treatment | no |
|-------------------------|----|

#### Connectivity

|                   |                 |
|-------------------|-----------------|
| Trunking coupling | without coupler |
|-------------------|-----------------|

#### Materials

|                           |                       |
|---------------------------|-----------------------|
| Colour                    | stone grey            |
| RAL colour                | RAL 7030 - Stone grey |
| Material                  | PC-ABS                |
| Material group            | plastic               |
| Type of surface treatment | untreated             |

#### Dimensions

|                 |          |
|-----------------|----------|
| Trunking height | 60 mm    |
| Trunking width  | 110 mm   |
| Profile height  | 40-60 mm |

#### Equipment

|                      |    |
|----------------------|----|
| With protective film | no |
|----------------------|----|

#### Standards

|                         |                      |
|-------------------------|----------------------|
| Approvals               | EN50085-2-1          |
| European directive RoHs | voluntary compliance |

#### Safety

|                 |      |
|-----------------|------|
| Halogen free    | yes  |
| Impact strength | IK07 |

#### Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...60 °C |
|-----------------------|------------|

#### temperatur

|                     |            |
|---------------------|------------|
| Ambient temperature | -5...60 °C |
|---------------------|------------|