



LFF6019007030

Trunking 60190, grey

Technische Merkmale

Architecture

Fixing mode	bottom punched
-------------	----------------

Functions

Suitable for functional integrity according to DIN 4102-12	no
--	----

Configuration

Antibacterial treatment	no
-------------------------	----

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	48
Maximum number of cables (Ø 11 mm, 50% fill)	48

Cover, door

Lid shape	loose
-----------	-------

Materials

RAL colour	RAL 7030 - Stone grey
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	no

Dimensions

Trunking height	60 mm
Length	2000 mm
Trunking width	190 mm
Distance bottom-punch along trunking-direction	125 mm
Distance bottom-punch crosswise trunking-direction	110 mm

Cable

Internal/useful cross section	9060 mm²
-------------------------------	----------

Scope of delivery

Delivery on roll	no
------------------	----

Equipment

Number of plugable separators	3
Compartment quantity	1 / 4
Cable retainers per meter	2
Cable fixing clips included	no
With protective film	no

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------