



BRP651304H9010

**Internal corner, BRP/BRAP65130, pure white**

Technische Merkmale

**Architecture**

Fixing mode	Clamping
-------------	----------

**Functions**

Overlapping	yes
-------------	-----

**Configuration**

Antibacterial treatment	no
-------------------------	----

Symetrical	yes
------------	-----

**Compatibility**

Product compatibility	BRP / BRAP
-----------------------	------------

**Connectivity**

Trunking coupling	without coupler
-------------------	-----------------

**Cover, door**

Lid with softlip	-
------------------	---

**Materials**

Colour	pure white
--------	------------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	PC-ABS
----------	--------

Material group	plastic
----------------	---------

Type of surface treatment	untreated
---------------------------	-----------

**Dimensions**

Trunking height	65 mm
-----------------	-------

Length	135 mm
--------	--------

Trunking width	130 mm
----------------	--------

**Installation, mounting**

Base punching	Without base punching
---------------	-----------------------

**Settings**

Angle range	85 / 95 °
-------------	-----------

**Accessories included**

Accessory configuration	Moulded
-------------------------	---------

**Equipment**

Cable fixing clips included	yes
-----------------------------	-----

With protective film	no
----------------------	----

<b>Standards</b>	
European directive RoHs	voluntary compliance
<b>Safety</b>	
Halogen free	yes
<b>Use conditions</b>	
Operating temperature	-30...90 °C
<b>temperatur</b>	
Ambient temperature	-30...90 °C