



Systo Cable outlet, black

WS155N

Architecture

Type of pole	0 P
Fixing mode	Recessed

Functions

Can be used as a switch	no
Overvoltage protection	no

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	no
--------------------------	----

Main electrical features

Frequency	50/60 Hz
Nominal voltage	400 V

Capacity

Number of modules for WA	2
--------------------------	---

Cover, door

Interlockable	no
---------------	----

Power supply

Special power supply	No special power supply
----------------------	-------------------------

Materials

RAL colour	RAL 9005 - Jet black
Material	Polycarbonate (PC)
Surface appearance	matt
Type of surface treatment	Painted

Dimensions

Depth of installed product	22,8 mm
Height of installed product	45 mm
Length	37 mm
Width of installed product	45 mm
Dimensions (LLxwwxhh)	45x45x37

Installation, mounting

Fixing type	Clipped
Mounting type	various

Connection

type of connection	with screw
Phase pickup	L1

Equipment

On/Off switch	no
Insulated	yes
Transparent product label holder	no

Standards

Approvals	NFC 61314
-----------	-----------

Safety

Protection index IP	21D
IK protection code against mechanical impacts	07
halogen free	yes
Glow wire test	according to CEI 695-2-1: 650°C

Identification

Range	systo
Version	Other