



## tehalit.HNG base and lid depth 25 mm

Description	Pack	Art No.
HNG 25025/0 Grey 7035 Trunking	<del>36</del>	<b>HNG2502507035B</b>

HNG2502507035B



## tehalit.HNG base and lid depth 40 mm

Description	Pack	Art No.
HNG 37025/0 Grey 7035 Trunking	<del>48</del>	<b>HNG3702507035B</b>
HNG 37037/0 Grey 7035 Trunking	32	<b>HNG3703707035B</b>
HNG 37050/0 Grey 7035 Trunking	40	<b>HNG3705007035B</b>

HNG3702507035B



## tehalit.HNG base and lid depth 50 mm

Description	Pack	Art No.
HNG 50025/0 Grey 7035 Trunking	<del>48</del>	<b>HNG5002507035B</b>
HNG 50037/0 Grey 7035 Trunking	40	<b>HNG5003707035B</b>
HNG 50050/0 Grey 7035 Trunking	48	<b>HNG5005007035B</b>
HNG 50075/0 Grey 7035 Trunking	20	<b>HNG5007507035B</b>
HNG 50100/0 Grey 7035 Trunking	24	<b>HNG5010007035B</b>
HNG 50125/0 Grey 7035 Trunking	18	<b>HNG5012507035B</b>

HNG5002507035B



## tehalit.HNG base and lid depth 75 mm

Description	Pack	Art No.
HNG 75037/0 Grey 7035 Trunking	<del>40</del>	<b>HNG7503707035B</b>
HNG 75050/0 Grey 7035 Trunking	20	<b>HNG7505007035B</b>
HNG 75075/0 Grey 7035 Trunking	16	<b>HNG7507507035B</b>
HNG 75100/0 Grey 7035 Trunking	16	<b>HNG7510007035B</b>
HNG 75125/0 Grey 7035 Trunking	12	<b>HNG7512507035B</b>

HNG7503707035B



HN370503

## tehalit.HNG clip

Description	Pack	Art No.
HN 37050/3 Retaining clip	<del>50</del>	<b>HN370503</b>
HN 50050/3 Retaining clip	50	<b>HN500503</b>
HN 50075/3 Retaining clip	50	<b>HN500753</b>
HN 50100/3 Retaining clip	50	<b>HN501003</b>
HN 50125/3 Retaining clip	50	<b>HN501253</b>
HN 75050/3 Retaining clip	50	<b>HN750503</b>
HN 75075/3 Retaining clip	50	<b>HN750753</b>
HN 75100/3 Retaining clip	50	<b>HN751003</b>
HN 75125/3 Retaining clip	50	<b>HN751253</b>