



VU48NE

Encl., Volta, flush, 4x12MOD, IP30

Technische Merkmale

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With a pipe-in lead	yes
---------------------	-----

Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Cover, door

Type of door closing	Latch
Identification of protection index	30
Interlockable	no
Cover type	With Notch
Door locking	without
Door leave	single
Door quantity	1
Cover type	Door
Transparent cover or door	no

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Dimensions

Insertion depth	89 mm
Depth of installed product	98 mm
Internal depth	91,5 mm
Height of installed product	755,5 mm
Installation height	720 mm
Length	755,5 mm
Width of installed product	348 mm
Width in division units	12
Thickness of sidewall material	2,5 mm
Built-in height	740 mm
Built-in width	314,5 mm

Installation, mounting

Suitable for outdoor use	no
--------------------------	----

Scope of delivery

With cover	no
------------	----

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of units	12
Number of rows	4
Quantity of section in width	1
Quantity of rails	4
Can be accessorized	yes
Extension possible	yes

Standards

GWT Glow wire test	650 °C
European directive WEEE	concerned
Protection class according to IEC-61140	II

Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP30
Protection class	isol.class II
Halogen free	yes
Impact strength	IK05
Ultraviolet resistant	yes

Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------