



WNC036

cubyko Key SW 3 positions wall M grey

Product Datasheet

Architecture

Type of control unit	Key
Number of keys	1
Fixing mode	Screwed

Main electrical features

Frequency	50/60 Hz
Nominal voltage	250 V

Materials

RAL colour	RAL 7011 - Iron grey
Colour	complete grey
Material	Polypropylen
Material	polypropylène
Type of surface treatment	mat

Dimensions

Depth of installed product	74 mm
Height of installed product	75 mm
Width of installed product	75 mm
Dimensions (LLxwxhh)	76x76x81

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of connection	quick connect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

Protection index IP	IP55
IK protection code against mechanical impacts	07

Use conditions

Storage temperature	-50 to 50 °C
---------------------	--------------

Identification

Composition	Complete installation with frame
Range	cubyko