



cubyko 2x hor. sock 2P+E wall M white

Product Datasheet

Architecture

Type of pole	2P+T
Fixing mode	Screwed

Functions

Centralized terminal connections	yes
With orientation lighting	no
Usable as a switch	no
Overvoltage protection	no

Configuration

Rotated central insert	no
------------------------	----

Controls and indicators

Indicator lamp	no
With or without indicator	without

Connectivity

With USB charging socket	no
Type of USB port	other

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	16 A
---------------	------

Capacity

Number of modules for WA	4
Number of module locations	4

Cover, door

Interlockable	no
---------------	----

Power supply

Special power supply	No special power supply
----------------------	-------------------------

WNC122B



WNE122B

Materials

Colour	complete white
Colour	white (shades)
RAL colour	RAL 9010 - Pure white
Material	Polypropylen
Surface appearance	satın finish
Surface protection	other
Type of surface treatment	mat varnish
Transparent	no

Dimensions

Depth of installed product	22,8 mm
Height of installed product	75 mm
Dimensions (LLxwwxhh)	76x76x96
Width of installed product	146 mm

Installation, mounting

Fixing type	With screws
Mounting type	surface

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Phase pickup	L1
Type of connection	Quickconnect

Accessories included

With miniature fuse	no
---------------------	----

Equipment

On/Off switch	no
With transparent product label holder	no

Standards

Approvals	NFC 61314
-----------	-----------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55
- without protective screen	

Use conditions

Operating temperature	-15...30 °C
Storage/transport temperature	-50...50 °C
Insulated	yes

Identification

Range	cubyko
-------	--------