



WNC003

cubyko 2W SW control light wall M grey

Product Datasheet

Architecture

Type of order	Switch
Type of control unit	single rocker
Number of keys	1
Fixing mode	Screwed

Controls and indicators

Indicator lamp	as an accessory
----------------	-----------------

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 AX
---------------	-------

Capacity

Number of modules for WA	2
--------------------------	---

Materials

Colour	complete grey
RAL colour	RAL 7011 - Iron grey
Material	polypropylène
Material	Polypropylen
Type of surface treatment	mat

Dimensions

Depth of installed product	64 mm
Height of installed product	75 mm
Dimensions (LLxwxhh)	76x76x65
Width of installed product	75 mm

Installation, mounting

Mounting type	surface
---------------	---------

Connection

Connection cross-sect. rigid cable	mini 2x1 mm ² - maxi 2x2,5 mm ²
Type of contacts	2 way
Type of connection	Quickconnect

Standards

Approvals	EN 60669-1
-----------	------------

Safety

IK protection code against mechanical impacts	07
Protection index IP	IP55

Identification

Range	W.1
Composition	Complete installation with frame