



MZ913

## Auto reclosing remote control auxiliary

Product Datasheet

### Main electrical features

Rated operational voltage Ue	207 / 230 / 253 V
Type of supply voltage	AC
Frequency	50/60 Hz

### Voltage

Rated insulation voltage	13 kV
Command voltage AC	207 / 230 / 253 V

### Electric current

Acceptable current rating with AC1	5 A
------------------------------------	-----

### Power

Total power loss under IN	0,11 W
---------------------------	--------

### Dimensions

Depth of installed product	71 mm
Height of installed product	83 mm
Width of installed product	52,5 mm

### Installation, mounting

Tightening torque	1,7Nm;0,6Nm
-------------------	-------------

### Connection

Connection cross-sect. flexible conductor	terminals 1 and 3 : 1 to 6mm <sup>2</sup> / terminals 2 up to 18 : 0,2 to 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	Terminals 1 and 2 : 1,5 / 10mm <sup>2</sup> - Terminals 2 up to 8 : 0,2 / 2,5mm <sup>2</sup>

### Equipment

Quantity of NO contacts	2
-------------------------	---

### Standards

European directive WEEE	concerned
-------------------------	-----------

### Safety

Dielectric properties distance between coil and contact	6Kv
---	-----

### Use conditions

Operating temperature	-5...40 °C
-----------------------	------------