



ESC080

Auxiliary contact 6A, 1NO+1NC

Product Datasheet

Main electrical features

Rated operational voltage U _e	230 V
--	-------

Voltage

Rated insulation voltage	240 V
Rated impulse withstand voltage	4 kV

Electric current

Acceptable current rating with AC1	6 A
Rated current	6 A

Power

Total power loss under I _N	0,1 W
---------------------------------------	-------

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	11 mm

Connection

Connection cross-sect. flexible conductor	1 / 6 mm ²
Connection cross-sect. rigid cable	1 / 6 mm ²
Number of contacts	2
Type of contacts	1NC+1NO
Type of connection	with screw
Cable connect. cross section (flexible) for control	1 / 6 mm ²
Connection cross-section of the control cable solid	1 / 10 mm ²

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C