



BRP652104DH9010

Internal corner, BRP/BRAP65210, pure white

Product Datasheet

Architecture

Fixing mode	Clamping
-------------	----------

Functions

Overlapping	yes
-------------	-----

Configuration

Antibacterial treatment	no
Symmetrical	yes

Compatibility

Product compatibility	BRP/BRAP
-----------------------	----------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Cover, door

Lid with softlip	-
------------------	---

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Material group	plastic
Type of surface treatment	Painted

Dimensions

Trunking height	65 mm
Length	135 mm
Trunking width	210 mm

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Settings

Angle range	85 / 95 °
-------------	-----------

Accessories included

Accessory configuration	Moulded
-------------------------	---------

Equipment

Cable fixing clips included	yes
With protective film	no

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Halogen free	yes
--------------	-----

Use conditions

Operating temperature	-30...90 °C
-----------------------	-------------

temperatur

Ambient temperature	-30...90 °C
---------------------	-------------