



VS112PF

Sm.distr, golf, surface, 12M, wh door

Product Datasheet

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	yes
---------------------	-----

Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Cover, door

Type of door closing	Latch
Identification od protection index	40
Interlockable	no
Cover type	Closed (plain)
Door locking	without
Door leave	single
Door quantity	1
Cover type	Door
Transparent cover or door	no

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Dimensions

Depth of installed product	99 mm
Internal depth	99 mm
Height of installed product	252 mm
Width of installed product	282 mm
Width in division units	12

Installation, mounting

Suitable for outdoor use	no
--------------------------	----

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	yes
Extension possible	yes

Standards

GWT Glow wire test	650 °C
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP40
Protection class	isol.class II
Halogen free	yes
Impact strength	IK07
Ultraviolet resistant	no

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------