



VS112TF1



VS112TF

Sm.distr, golf, surface, 12M, transp. door

Product Datasheet

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead yes

Compatibility

Compatible with DIN rail mounting yes

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Cover, door

Type of door closing Latch

Identification od protection index 40

Interlockable no

Cover type Closed (plain)

Door locking without

Door leave single

Door quantity 1

Cover type Door

Transparent cover or door yes

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

Dimensions

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 252 mm

Width of installed product 282 mm

Width in division units 12

Installation, mounting

Suitable for outdoor use no

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	yes
Extension possible	yes

Standards

GWT Glow wire test	650 °C
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP40
Protection class	isol.class II
Halogen free	yes
Ultraviolet resistant	no

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------