



VS112PJ1



VS112PJ

Sm.distr, golf, surface, 12M, wh door

Product Datasheet

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead yes

Compatibility

Compatible with DIN rail mounting yes

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Cover, door

Type of door closing Latch

Identification od protection index 40

Interlockable no

Cover type Closed (plain)

Door locking without

Door leave single

Door quantity 1

Cover type Door

Transparent cover or door no

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

Dimensions

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 252 mm

Width of installed product 282 mm

Width in division units 12

Installation, mounting

Suitable for outdoor use no

Accessories included

| | |
|-------------------------|----|
| Mounting plate included | no |
| With lock | no |

Equipment

| | |
|------------------------------|-----|
| Number of rows | 1 |
| Quantity of section in width | 1 |
| Quantity of rails | 1 |
| Can be accessorized | yes |
| Extension possible | yes |

Standards

| | |
|-------------------------|-----------|
| GWT Glow wire test | 650 °C |
| European directive WEEE | concerned |

Safety

| | |
|---|---------------|
| IK protection code against mechanical impacts | IK07 |
| Protection index IP | IP40 |
| Protection class | isol.class II |
| Halogen free | yes |
| Ultraviolet resistant | no |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25...40 °C |
|-----------------------|-------------|