



VS412PF

**Sm.distr, golf, surface, 48M, wh door**

Product Datasheet

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Functions

With a pipe-in lead	yes
---------------------	-----

### Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

### Main electrical features

Nominal voltage	400 V
-----------------	-------

### Electric current

Rated current	63 A
---------------	------

### Cover, door

Type of door closing	Latch
Identification od protection index	40
Interlockable	no
Cover type	Closed (plain)
Door locking	without
Door leave	single
Door quantity	1
Cover type	Door
Transparent cover or door	no

### Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

### Dimensions

Depth of installed product	99 mm
Internal depth	99 mm
Height of installed product	647 mm
Width of installed product	282 mm
Width in division units	12

### Installation, mounting

Suitable for outdoor use	no
--------------------------	----

## Accessories included

Mounting plate included	no
With lock	no

## Equipment

Number of rows	4
Quantity of section in width	1
Quantity of rails	4
Can be accessorized	yes
Extension possible	yes

## Standards

GWT Glow wire test	650 °C
European directive WEEE	not concerned

## Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP40
Protection class	isol.class II
Halogen free	yes
Ultraviolet resistant	no

## Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------