



FWB31S

FWB encl., univers, IP44,500x300x161mm, QC

Product Datasheet

Architecture

Fixing mode flush-mounting/surface-mounting/section make

Functions

With a pipe-in lead yes

Compatibility

Compatible with DIN rail mounting yes

Cover, door

Cover type With Notch

Lid shape Closed

Transparent cover or door no

Cover type Cover

Type of door closing hinged pattern handle

Door quantity 1

Number of keylock of the door 1

Materials

Copper weight of the product 0,036 kg

Colour white

Colour white

Material sheet steel

Enclosure material steel

Material housing Steel

Type of surface treatment powder-coated

Dimensions

Depth of installed product 161 mm

Height of installed product 500 mm

Width of installed product 300 mm

Accessories included

Fitted with with clamp

Equipment

Number of rows 3

Quantity of section in width 1

Can be accessorized yes

Quantity of rails 3

Standards

Protection class according to IEC-61140 II

Protection degree and standard for type plate IP44 - EN 60529 --- IP44 - DIN VDE 0470-1

Product standard low-voltage for type plate VDE 0660-600-2/-3

Safety

Protection class	isol.class II
Protection index IP	IP44
IK protection code against mechanical impacts	09
Impact strength	IK09