



FWB encl., univers, IP44,500x800x161mm, QC

FWB33S

#### Architecture

Fixing mode	flush-mounting/surface-mounting/ section make
-------------	--

#### Functions

With a pipe-in lead	yes
---------------------	-----

#### Cover, door

Cover type	With Notch
Lid shape	Closed
Transparent cover or door	no
Cover type	Cover
Type of door closing	hinged pattern handle and
Number of doors	2
Number of keylock of the door	1

#### Materials

Copper weight of the product	0,103 kg
Colour	white
Colour	white
Material	sheet steel
Enclosure material	steel
Material housing	Steel
Type of surface treatment	powder-coated

#### Dimensions

Depth of installed product	161 mm
Height of installed product	500 mm

#### Installation, mounting

Suitable for outdoor mounting	No
-------------------------------	----

**Accessories included**

accessorizable	yes
----------------	-----

**Equipment**

Number of rows	9
Quantity of section in width	3
Quantity of rails	9

**Standards**

Protection class according to IEC-61140	II
protection degree and standard for type plate	IP44 - EN 60529 --- IP44 - DIN VDE 0470-1
product standard low-voltage for type plate	VDE 0660-600-2/-3

**Safety**

Protection class	isol.class II
Protection index IP	IP44
Impact strength	IK09