

**FWB encl., univers, IP44,500x1050x161, QC**

Product Datasheet

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Cover, door**

Cover type	Closed (plain)
Transparent cover or door	yes
Cover type	Door
Material thickness cover	1 mm
Type of door closing	hinged pattern handle
Door leave	double asymmetric
Door quantity	2
Number of keylock of the door	1

**Materials**

RAL colour	RAL 9010 - Pure white
Colour	white
Material	Steel
Type of surface treatment	powder-coated

**Dimensions**

Depth of installed product	161 mm
Internal depth	161 mm
Height of installed product	500 mm
Width of installed product	1050 mm
Width in division units	12
Thickness of sidewall material	1 mm

**Installation, mounting**

Suitable for outdoor use	no
--------------------------	----

**Accessories included**

Mounting plate included	no
With lock	no

**Equipment**

Number of openings for flange plates	8
Number of rows	12
Quantity of section in width	4
Extension possible	yes
Quantity of rails	12

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection class	isol.class II
Protection index IP	IP44
IK protection code against mechanical impacts	IK07
Fire resistance	-