



FWB52GS

FWB encl., univers, IP44,800x550x161, QC

Product Datasheet

#### Architecture

Fixing mode	flush-mounting/surface-mounting/section make
-------------	----------------------------------------------

#### Configuration

Module	with terminals
--------	----------------

#### Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

#### Electric current

Rated current	125 A
---------------	-------

#### Cover, door

Type of door closing	hinged pattern handle
Number of keylock of the door	1
Cover type	With Notch
Door leave	single
Door quantity	1
Cover type	Door
Transparent cover or door	yes

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

#### Dimensions

Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	800 mm
Installation height	800 mm
Width of installed product	550 mm
Width in division units	12

#### Installation, mounting

Suitable for outdoor use	no
--------------------------	----

#### Accessories included

Mounting plate included	no
With lock	no

## Equipment

Number of rows	10
Quantity of section in width	2
Number of keys	1
Quantity of rails	10
Can be accessorized	yes
Extension possible	yes

## Standards

European directive WEEE	concerned
-------------------------	-----------

## Safety

Protection index IP	IP44
Protection class	isol.class II