



FWB53GS

FWB encl., univers, IP44,800x800xx161, QC

Product Datasheet

Architecture

Fixing mode surface-mounting

Cover, door

Cover type With Notch

Transparent cover or door yes

Cover type Door

Material thickness cover 1 mm

Type of door closing hinged pattern handle

Door leave double asymmetric

Door quantity 2

Number of keylock of the door 1

Materials

RAL colour RAL 9010 - Pure white

Colour white

Material Steel

Type of surface treatment powder-coated

Dimensions

Depth of installed product 161 mm

Internal depth 161 mm

Height of installed product 800 mm

Width of installed product 800 mm

Width in division units 12

Thickness of sidewall material 1 mm

Installation, mounting

Suitable for outdoor use no

Accessories included

Mounting plate included no

With lock no

Equipment

Number of openings for flange plates 6

Number of rows 15

Quantity of section in width 3

Extension possible yes

Quantity of rails 15

Standards

European directive WEEE concerned

Safety

Protection class	isol.class II
Protection index IP	IP44
IK protection code against mechanical impacts	IK07
Fire resistance	-