



HBD401H

RCD add on h400 4P 400A I_{dn} adj

Product Datasheet

Architecture

Number of poles 4 P

Main electrical features

Frequency 50/60 Hz

Rated operational voltage U_e 220/415 V

Voltage

Rated insulation voltage 500 V

Rated impulse withstand voltage 6000 V

Electric current

Rated residual operating current 30/100/300 mA/1/3/6 A

Power

Power loss per pole at I_n 8 W

Total power loss under I_N 24 W

Connection

Connection cross-sect. rigid cable 240 mm²

Settings

Rated fault current adjustable no

Delay adjustable yes

Time delay of residual current 0/0,06/0,15/0,3/0,5/1 s

Standards

Standard text IEC 60947-2

European directive WEEE concerned

Safety

Residual current type A