



HXC025H

Aux low lvl 1NO+NC 125V AC(h250...1600)

Product Datasheet

Architecture

| | |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 125 V |
|------------------------------|-------|

Voltage

| | |
|---------------------------------|------|
| Rated operational voltage in DC | 30 V |
|---------------------------------|------|

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 3 W |
|---------------------------|-----|

Connection

| | |
|--------------------|------------|
| Type of connection | with screw |
|--------------------|------------|

| | |
|------------------|---------|
| Type of contacts | 1 NO/NC |
|------------------|---------|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP4X |
|---------------------|------|

Use conditions

| | |
|--|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
|--|---|

| | |
|----------|--------|
| Altitude | 2000 m |
|----------|--------|