

UVR delayed h250-h630 24V DC

Product Datasheet

Voltage

| | |
|---------------------------------|------|
| Rated operational voltage in DC | 24 V |
|---------------------------------|------|

Power

| | |
|-----------------------|---------|
| Inrush power absorbed | 0,53 VA |
|-----------------------|---------|

| | |
|---------------------------|-------|
| Total power loss under IN | 0,5 W |
|---------------------------|-------|

Connection

| | |
|--------------------|------------|
| Type of connection | with screw |
|--------------------|------------|

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP4X |
|---------------------|------|

Use conditions

| | |
|--|---|
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
|--|---|

| | |
|----------|--------|
| Altitude | 2000 m |
|----------|--------|