



HXC026H

AL contact low level 1NO+NC(h250...1600)

Product Datasheet

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Rated operational voltage Ue	125 V
------------------------------	-------

Voltage

Rated operational voltage in DC	30 V
---------------------------------	------

Power

Total power loss under IN	3 W
---------------------------	-----

Connection

Type of contacts	1 NO/NC
Type of connection	with screw

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP4X
---------------------	------

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m