



kallystaCeiling loudspeaker 2"

WUZ672

Functions

Loudness control	no
------------------	----

Main electrical features

Frequency	120 - 20000 Hz
-----------	----------------

Frequency

Frequency range audio	200 Hz - 16 kHz
Frequency band	200/16000 Hz
Frequency response (-3 dB)	200 - 16000 Hz

Power

Nominal/music power handling	3/4 W
------------------------------	-------

Resistance

Impedance	20 ?
-----------	------

Materials

Colour	white
Material	metal

Dimensions

Insertion depth	35 mm
Depth of installed product	29 mm
Internal depth	29 mm
Installation opening Ø	68 mm
Recommended installation height	2,4 - 4 m
Installation wall thickness	15 mm

Installation, mounting

Built-in	yes
Mounting Method	Surface

- with spring mechanism for ceiling installation

Connection

Conductor cross-section (flexible)	max. 1,5 mm ²
- with screw terminal	

Equipment

Sound pressure level 1 W/1 m	82 dB
Sound pressure level at rated power	87 dB

Standards

Approvals	CE
-----------	----

Identification

Main design line	Communication technology
------------------	--------------------------

Instructions

- Housing screws made of stainless steel.
