



LS431

## Fuse carrier 1P 25A L31 signal light 1M

Product Datasheet

### Architecture

Type of pole	1 P
--------------	-----

### Voltage

Rated insulation voltage	690 V
--------------------------	-------

### Electric current

Rated current	25 A
---------------	------

### Fuse

CharactFuse	gG, aM
-------------	--------

### Power

Total power loss under IN	3,1 W
---------------------------	-------

### Dimensions

Depth of installed product	75 mm
Height of installed product	83 mm
Width of installed product	18 mm

### Installation, mounting

Tightening torque	2,2Nm
-------------------	-------

### Standards

European directive WEEE	concerned
-------------------------	-----------

### Safety

Protection index IP	IP20
---------------------	------

### Use conditions

Operating temperature	-5...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C