



LS531

## Fuse carrier 1P 32A L38 signal light 1M

Product Datasheet

### Architecture

Type of pole	1 P
--------------	-----

### Electric current

Rated current	32 A
---------------	------

### Fuse

CharactFuse	gG, aM
-------------	--------

### Power

Total power loss under IN	3,7 W
---------------------------	-------

### Dimensions

Depth of installed product	75 mm
Height of installed product	83 mm
Width of installed product	18 mm

### Installation, mounting

Tightening torque	2,2Nm
-------------------	-------

### Connection

Connection cross-section of input and output with screws, for massive conductors	1 / 25 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	0,75 / 16 mm <sup>2</sup>

### Standards

European directive WEEE	concerned
-------------------------	-----------

### Safety

Protection index IP	IP20
---------------------	------

### Use conditions

Operating temperature	-5...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C