



L53201

Fuse carrier 1P+N 32A L38 sign. light 1M

Product Datasheet

Architecture

Number of poles	2 P
Type of pole	1P+N

Electric current

Rated current	32 A
---------------	------

Fuse

CharactFuse	gG
-------------	----

Power

Total power loss under IN	1,5 W
---------------------------	-------

Dimensions

Depth of installed product	75 mm
Height of installed product	77 mm
Width of installed product	17,5 mm

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C