



LR604

Fuse carrier 3P+N 50A L51 6M

Product Datasheet

Architecture

Number of poles	4 P
Type of pole	3P+N

Electric current

Rated current	50 A
---------------	------

Fuse

CharactFuse	gG, aM
-------------	--------

Power

Total power loss under IN	20,6 W
---------------------------	--------

Dimensions

Depth of installed product	93 mm
Height of installed product	107 mm
Width of installed product	105 mm

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C