



Trunking 16x30, L=2,1m, pure white

Product Datasheet

Architecture

Fixing mode bottom punched

Functions

Suitable for functional integrity according to DIN 4102-12 no

Configuration

Antibacterial treatment no

Connectivity

Trunking coupling without coupler

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 2

Maximum number of cables (Ø 11 mm, 50% fill) 1

Cover, door

Lid shape premounted

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material PVC

Material group plastic

Type of surface treatment untreated

Transparent no

Dimensions

Trunking height 16 mm

Length 2100 mm

Trunking width 32 mm

Installation, mounting

Base punching Without base punching

Cable

Number of wires 1,5 mm² - 40% filling degree 28

Internal/useful cross section 420 mm²

Number of wires 2,5 mm² - 40% filling degree 22

Scope of delivery

Delivery on roll no

ATA163019010



Equipment

Number of fix dividers	1
Compartment quantity	2
Cable retainers per meter	2
Cable fixing clips included	yes
With protective film	no

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	-5...65 °C
-----------------------	------------