



Trunking 16x30, L=2,1m, brown

Product Datasheet

Architecture

Fixing mode	bottom punched
-------------	----------------

Functions

Suitable for functional integrity according to DIN 4102-12	no
--	----

Configuration

Antibacterial treatment	no
-------------------------	----

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	1
Maximum number of cables (Ø 11 mm, 50% fill)	1

Cover, door

Lid shape	premounted
-----------	------------

Materials

Colour	brown
RAL colour	RAL 8014 - Sepia brown
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	no

Dimensions

Trunking height	16 mm
Length	2100 mm
Trunking width	32 mm

Cable

Number of wires 1,5 mm ² - 40% filling degree	28
Internal/useful cross section	420 mm ²
Number of wires 2,5 mm ² - 40% filling degree	22

Scope of delivery

Delivery on roll	no
------------------	----

ATA163018014

Equipment

Number of fix dividers	1
Cable retainers per meter	2
Cable fixing clips included	yes
With protective film	no

Standards

Approvals	EN50085-2-1
European directive RoHs	voluntary compliance

Safety

Protection index IP	IP40
Halogen free	no
Impact strength	IK07

Use conditions

Operating temperature	-5...65 °C
-----------------------	------------