



**Trunking base SL200551 black**

Product Datasheet

**Capacity**

Cable capacity 11 mm D e.g. NYM 3 x 1.5mm <sup>2</sup> 1st chamber	2 Part
Cable capacity 11 mm D e.g. NYM 3 x 1.5mm <sup>2</sup> 2nd chamber	3 Part
Maximum number of cables (Ø 11 mm, 50% fill)	4

**Materials**

Colour	black
Material	PVC
Material group	plastic
Type of surface treatment	Other

**Dimensions**

Length	2000 mm
Trunking height	55 mm
Trunking width	20 mm

**Cable**

Number of wires 1,5 mm <sup>2</sup> - 40% filling degree	44
Number of wires 2,5 mm <sup>2</sup> - 40% filling degree	32

**Equipment**

Number of fix dividers	1
Compartment quantity	2

**Use**

Product type as headline for catalogue	Base
--	------

**Standards**

Approvals	CE
European directive RoHs	voluntary compliance

**Safety**

Halogen free	no
--------------	----

**temperatur**

Ambient temperature	-5 ... 65 °C
---------------------	--------------

**Identification**

Range name	tehalit SL
------------	------------

SL200551

