



G4796

Connecting line Wago 3x2,5 ² L=1,5m

Product Datasheet

Architecture

Connection system	Wago Winsta
-------------------	-------------

Connectivity

Number of wires	3
-----------------	---

Main electrical features

Nominal voltage	230 V
-----------------	-------

Electric current

Rated current	20 A
---------------	------

Length

Total length	1,5 m
--------------	-------

Power

Fire load	4497 kJ
-----------	---------

Resistance

Continuity resistor	1330 $\mu\Omega$
---------------------	------------------

Materials

Colour	black
Colour coding / contact insert	black
Colour housing	black
Colour outer sheath	Black
Material	Mixed materials
Material group	mixed material
Type of surface treatment	coated

Dimensions

Length	1500 mm
--------	---------

Connection

Cross section connection cable	2,5 mm ²
Type of finished cable	Connecting cable

Cable

Wire cross-section	2,5 mm ²
Cable permanent temperature-resistant to	70 °C
Cable diameter	13 mm
Conductor cross-section	2,5 mm ²

Equipment

Type side 1	Bus
Mechanical coding	yes
Type side 2	Plug

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
Halogen free	no

temperatur

Insulating piece permanent temperature-resistant	105 °C
--	--------