



G4798

connection line Wago 3x2,5² L=4,5m

Product Datasheet

Architecture

Connection system Wago Winsta

Connectivity

Number of wires 3

Main electrical features

Nominal voltage 230 V

Electric current

Rated current 20 A

Length

Total length 4,5 m

Power

Fire load 12462 kJ

Resistance

Continuity resistor 1330 µΩ

Materials

Colour black

Colour coding / contact insert black

Colour housing black

Colour outer sheath Black

Material Mixed materials

Material group mixed material

Type of surface treatment coated

Dimensions

Length 4500 mm

Connection

Cross section connection cable 2,5 mm²

Type of finished cable Connecting cable

Cable

Wire cross-section 2,5 mm²

Cable permanent temperature-resistant to 70 °C

Cable diameter 13 mm

Conductor cross-section 2,5 mm²

Equipment

Type side 1	Bus
Mechanical coding	yes
Type side 2	Plug

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
Halogen free	no

temperatur

Insulating piece permanent temperature-resistant	105 °C
--	--------