



Systo 2M 2poles switch

WS008



Architecture

Type of order	Switch
Number of poles	2 P
Type of control unit	single rocker
Fixing mode	Recessed

Controls and indicators

Indicator lamp	no
----------------	----

Main electrical features

Frequency	50/60 Hz
Nominal voltage	250 V

Capacity

Number of modules for WA	2
--------------------------	---

Materials

RAL colour	RAL 9010 - Pure white
Colour	white
Material	Polycarbonate (PC)
Type of surface treatment	mat

Dimensions

Depth of installed product	33 mm
Height of installed product	45 mm
Width of installed product	45 mm
Dimensions (LLxwwxhh)	45x45x33

Connection

type of connection	quick connect
Type of contacts	2 poles

Equipment

Transparent product label holder	no
Marking	no

Standards

Approvals	EN 60669-1
-----------	------------

Safety

Protection index IP	IP31D
IK protection code against mechanical impacts	07
Glow wire test	according to NFC-20455 : 960°C

Use conditions

Storage temperature	-10 to 50 °C
---------------------	--------------

Identification

Range	systo
-------	-------