



## Systo 1M PB 10+1F w. light

WS030



### Architecture

Type of order	push button
Type of control unit	Push button
Number of keys	1
Fixing mode	Recessed

### Controls and indicators

Indicator lamp	as an accessory
----------------	-----------------

### Main electrical features

Frequency	50/60 Hz
Nominal voltage	250 V

### Capacity

Number of modules for WA	1
--------------------------	---

### Materials

RAL colour	RAL 9010 - Pure white
Colour	white
Material	Polycarbonate (PC)
Material	polycarbonate
Type of surface treatment	mat

### Dimensions

Depth of installed product	33 mm
Height of installed product	45 mm
Width of installed product	22 mm
Dimensions (LLxwxhh)	22.5x45x33

### Installation, mounting

Fixing type	Clipped
-------------	---------

#### Connection

type of connection	quick connect
Type of contacts	1NC+1NO

#### Equipment

Transparent product label holder	no
Marking	no

#### Standards

Approvals	EN 60669-1
-----------	------------

#### Safety

Protection index IP	IP31D
IK protection code against mechanical impacts	07
Glow wire test	according to NFC-20455 : 960°C

#### Use conditions

Storage temperature	-10 to 50 °C
---------------------	--------------

#### Identification

Range	systo
-------	-------