



NRF0012A00

Empty module 12x22,5

Product Datasheet

Functions

Overvoltage protection	no
------------------------	----

Configuration

Antibacterial treatment	no
-------------------------	----

Connectivity

With USB charging socket	no
--------------------------	----

Main electrical features

Nominal voltage	250 V
-----------------	-------

Type of supply voltage	AC
------------------------	----

Electric current

Rated current	16 A
---------------	------

Materials

Colour	aluminium
--------	-----------

Material	Aluminium
----------	-----------

Material group	aluminium
----------------	-----------

Dimensions

Height of installed product	56,5 mm
-----------------------------	---------

Length	310 mm
--------	--------

Width of installed product	54 mm
----------------------------	-------

Installation, mounting

Mounting type	flush
---------------	-------

Equipment

Number of connection cables	max. 2
-----------------------------	--------

Extension possible	no
--------------------	----

Use

Folding	no
---------	----

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
---------------------	------

Halogen free	yes
--------------	-----

Use conditions

Operating temperature	0...25 °C
-----------------------	-----------

Shape

Shape	Square
-------	--------