



NRF0020A00

Empty module 20x22,5

Product Datasheet

Functions

Overvoltage protection	no
------------------------	----

Configuration

Antibacterial treatment	no
-------------------------	----

Connectivity

With USB charging socket	no
--------------------------	----

Main electrical features

Nominal voltage	250 V
Type of supply voltage	AC

Electric current

Rated current	16 A
---------------	------

Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

Dimensions

Height of installed product	56,5 mm
Length	490 mm
Width of installed product	54 mm

Installation, mounting

Mounting type	flush
---------------	-------

Equipment

Number of connection cables	max. 2
Extension possible	no

Use

Folding	no
---------	----

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP20
Halogen free	yes

Use conditions	
Operating temperature	0...25 °C
Shape	
Shape	Square