



NRF0023D00

module 3 outl.,2 outl. lckd, connect.Wago

Product Datasheet

#### Architecture

Connection system	Wago Winsta
-------------------	-------------

#### Functions

Overvoltage protection	no
------------------------	----

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

Type of supply voltage	AC
------------------------	----

#### Electric current

Rated current	16 A
---------------	------

#### Power

Power	max. 3680 W
-------	-------------

#### Materials

Colour	aluminium
--------	-----------

Material	Aluminium
----------	-----------

Material group	aluminium
----------------	-----------

#### Dimensions

Height of installed product	55 mm
-----------------------------	-------

Length	330 mm
--------	--------

Width of installed product	55 mm
----------------------------	-------

#### Installation, mounting

Mounting type	surface
---------------	---------

#### Connection

Cross section connection cable	2,5 mm <sup>2</sup>
--------------------------------	---------------------

#### Equipment

Number of connection cables	max. 1
-----------------------------	--------

Number of household socket outlets	3
------------------------------------	---

Extension possible	no
--------------------	----

#### Use

Folding	no
---------	----

#### Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

**Safety**

Protection index IP	IP20
Halogen free	yes

**Shape**

Shape	Square
-------	--------