



NRF0204B00

module 4 outlets, 2x22,5 empty

Product Datasheet

Functions

|                        |    |
|------------------------|----|
| Overvoltage protection | no |
|------------------------|----|

Main electrical features

|                        |       |
|------------------------|-------|
| Nominal voltage        | 250 V |
| Type of supply voltage | AC    |

Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Power

|       |             |
|-------|-------------|
| Power | max. 3680 W |
|-------|-------------|

Materials

|                |           |
|----------------|-----------|
| Colour         | aluminium |
| Material       | Aluminium |
| Material group | aluminium |

Dimensions

|                             |        |
|-----------------------------|--------|
| Height of installed product | 55 mm  |
| Length                      | 265 mm |
| Width of installed product  | 55 mm  |

Installation, mounting

|               |         |
|---------------|---------|
| Mounting type | surface |
|---------------|---------|

Connection

|                                |                     |
|--------------------------------|---------------------|
| Cross section connection cable | 2,5 mm <sup>2</sup> |
|--------------------------------|---------------------|

Equipment

|                                    |        |
|------------------------------------|--------|
| Number of connection cables        | max. 1 |
| Number of appliances to build in   | 2      |
| Number of household socket outlets | 4      |
| Extension possible                 | yes    |

Use

|         |    |
|---------|----|
| Folding | no |
|---------|----|

Standards

|                         |                      |
|-------------------------|----------------------|
| European directive RoHs | voluntary compliance |
|-------------------------|----------------------|

Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP20 |
| Halogen free        | yes  |

| Shape |        |
|-------|--------|
| Shape | Square |